

Sickel opening device



SPECK Pumpen supplies practical opening devices for the BADU swimming pool circulation pumps. Toggle screws or cap nuts, partly exposed to corrosion, are therefore a thing of the past. The strainer tank lid can be opened easily with just one handle. There are three different universal opening aids, which cover the whole range of product types in the BADU series. The sickel opening device is attached to three of the cams on the side of the pre-filter lid. The lid is released by turning it in an anti-clockwise direction. It can be used for the BADU Eco Touch-Pro, BADU TOP and Bettar.

Downloads

- [Catalogue page](#)
- [Dimensional drawing](#)